

CUSTOMER SERVICE SOLUTION

All about the plastic injection molding





Benefit from our cooperation:



Reliable:

- Defined service scope
- Qualified professionals
- Continuous support from start to end

improvement



Solution-oriented:

- Fast response times
- Tailor-made service packages
- High customer orientation and flexibility



Competent:

- Simulation for optimal design
- Consulting and training by experts
- Pragmatic and practical solutions



Value-adding:

- Deep application know-how for consulting
- Process optimization and cost reduction
- Higher productivity and overall system efficiency



Compliance with standards:

- Our calibrations meet ISO 17025 standards and requirements such as IATF 16949, as well as other relevant norms and guidelines
- ISO 21001 certified Kistler Academy for our training sessions



YOUR SERVICE OF CHOICE:

Reliable protection and optimized performance

	Service agreement		Order number	Order key
	Service agreement	Your service package tailored to your needs	On request	service@kistler.com
	Software maintenance contract	AkvisIO IME Annual license maintenance contract	On request	2878AI / 2878AA
	Operation & Improvements	ARVISIO IIVIE Allitudi license maintenance contract	Order number	Order key
		Optimize and validate your injection molding process before commissioning by	Order Hulliber	Order key
	Risk process analysis standard	deriving sensor positioning based on the filling phase.	44002541	9968B21
	Professional	Includes standard, additional: holding pressure phase and thermals	44002542	9968B21
	Premium	Includes professional, additionally: first theoretical parameters or theoretical reference WID curve	44002543	9968B21
	Stasa QC Workshop	Work point optimization, 1 day on site	44000412	9968B21-D1-3
	Commissioning		Order number	Order key
	Hardware	e.g. a ComoNeos and/or senors on site 1/2 day	44002109	9962B21-D3-1-1
		e.g. ComoNeo and/or sensors on site 1 day	44002109	9962B21-D3-1-2
	Features	Multiflow (Hot runner controller & ComoNeo) 1 day	44002109	9962B21-D3-4-2
		z.B Switch , Predict, Merge, Composite (n. effort hours.)	44000158	
	Fieldservices		Order number	Order key
	Mold Validation I	Inspection of the installation and functioning of Kistler tool sensors incl. test certificate, 1/2 day on site	44002564	9962B21-MV1-0
		Inspection of the installation and functionality of Kistler tool sensors incl. test certificate, 1 day on site	44002565	9962B21-MV1-1
	Mold Validation II	Support for sampling tools with Kistler sensors, 1/2 day on site	44002566	9962B21-MV2-0
		Support for sampling tools with Kistler sensors, 1 day on site	44002567	9962B21-MV1-1
	Next day for Mold Validation II	max. 5 hours on site, incl. travel expenses	44001815	9968B21-D1-2
	Emergency Assistance		Order number	Order key
	Emergency Assistance Sensors / Test Pen	Verification and function test incl. diagnostic report	Order number 44002084	Order key
		Verification and function test incl. diagnostic report Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo		Order key
	Sensors / Test Pen	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C,	44002084	Order key
	Sensors / Test Pen Electronic Devices	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days	44002084 44002090	Order key
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency	44002084 44002090 44002632	Order key 9968B21-D1-4
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday).	44002084 44002090 44002632 44002441	9968B21-D1-4
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday).	44002084 44002090 44002632 44002441 44000353	
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours)	44002084 44002090 44002632 44002441 44000353 Order number	9968B21-D1-4
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house	44002084 44002090 44002632 44002441 44000353 Order number 44002124	9968B21-D1-4 Order key
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house	44002084 44002090 44002632 44002441 44000353 Order number 44002124 44002122	9968B21-D1-4 Order key 9961E-SC-04-00-0-X On-site max.8 TN
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house DIN ISO 21001 certified	44002084 44002090 44002632 44002441 44000353 Order number 44002124 44002122 In-house	9968B21-D1-4 Order key 9961E-SC-04-00-0-X
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo Kistler Academy	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house DIN ISO 21001 certified Basics of cavity pressure (theory and practice), 1 day	44002084 44002090 44002632 44002441 44000353 Order number 44002124 44002122 In-house Order number	9968B21-D1-4 Order key 9961E-SC-04-00-0-X On-site max.8 TN Order key
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo Kistler Academy P1 Training cavity pressure	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house DIN ISO 21001 certified Basics of cavity pressure (theory and practice), 1 day Installing cavity pressure sensors correctly (theory and practice), 1 day	44002084 44002090 44002632 44002441 44000353 Order number 44002124 44002122 In-house Order number 44002810 44002814	9968B21-D1-4 Order key 9961E-SC-04-00-0-X On-site max.8 TN Order key 44002811
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo Kistler Academy P1 Training cavity pressure P2 Sensor installation	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house DIN ISO 21001 certified Basics of cavity pressure (theory and practice), 1 day Installing cavity pressure sensors correctly (theory and practice), 1 day Working with the ComoNeo process monitoring system (theory and practice), 1 day	44002084 44002090 44002632 44002441 44000353 Order number 44002124 44002122 In-house Order number 44002810	9968B21-D1-4 Order key 9961E-SC-04-00-0-X On-site max.8 TN Order key 44002811 44002815
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo Kistler Academy P1 Training cavity pressure P2 Sensor installation P3 Training ComoNeo P4 Training process data storage	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house DIN ISO 21001 certified Basics of cavity pressure (theory and practice), 1 day Installing cavity pressure sensors correctly (theory and practice), 1 day Working with the ComoNeo process monitoring system (theory and practice), 1 day Management and use of the process data storage solution AkvislO IME, 1 day	44002084 44002090 44002632 44002441 44000353 Order number 44002124 44002122 In-house Order number 44002810 44002814 44002818	9968B21-D1-4 Order key 9961E-SC-04-00-0-X On-site max.8 TN Order key 44002811 44002815 44002819
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo Kistler Academy P1 Training cavity pressure P2 Sensor installation P3 Training ComoNeo P4 Training process data storage Q1 Quality in injection molding I	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house DIN ISO 21001 certified Basics of cavity pressure (theory and practice), 1 day Installing cavity pressure sensors correctly (theory and practice), 1 day Working with the ComoNeo process monitoring system (theory and practice), 1 day Management and use of the process data storage solution AkvislO IME, 1 day Quality in injection molding I, 2 days	44002084 44002090 44002632 44002441 44000353 Order number 44002124 44002122 In-house Order number 44002810 44002818 44002822	9968B21-D1-4 Order key 9961E-SC-04-00-0-X On-site max.8 TN Order key 44002811 44002815 44002819 44002823
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo Kistler Academy P1 Training cavity pressure P2 Sensor installation P3 Training ComoNeo P4 Training process data storage Q1 Quality in injection molding I Q2 Quality in injection molding II	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house DIN ISO 21001 certified Basics of cavity pressure (theory and practice), 1 day Installing cavity pressure sensors correctly (theory and practice), 1 day Working with the ComoNeo process monitoring system (theory and practice), 1 day Management and use of the process data storage solution AkvisIO IME, 1 day Quality in injection molding I, 2 days Quality in injection molding I, 3 days	44002084 44002090 44002632 44002441 44000353 Order number 44002122 In-house Order number 44002810 44002814 44002818 44002822 44002796 44002800	9968B21-D1-4 Order key 9961E-SC-04-00-0-X On-site max.8 TN Order key 44002811 44002815 44002819 44002823 44002797 44002801
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo Kistler Academy P1 Training cavity pressure P2 Sensor installation P3 Training ComoNeo P4 Training process data storage Q1 Quality in injection molding II Q3 Quality in injection molding III	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house DIN ISO 21001 certified Basics of cavity pressure (theory and practice), 1 day Installing cavity pressure sensors correctly (theory and practice), 1 day Working with the ComoNeo process monitoring system (theory and practice), 1 day Management and use of the process data storage solution AkvisIO IME, 1 day Quality in injection molding I, 2 days Quality in injection molding I, 3 days Consolidation of the seminar Quality molding 1 and 2, 2 days	44002084 44002090 44002632 44002441 44000353 Order number 44002124 44002122 In-house Order number 44002810 44002814 44002818 44002822 44002796 44002800 44002804	9968B21-D1-4 Order key 9961E-SC-04-00-0-X On-site max.8 TN Order key 44002811 44002815 44002819 44002823 44002797 44002801 44002805
	Sensors / Test Pen Electronic Devices Emergency Stock On-site within 3 days Remote Support Emergency Assistance Sensors ComoNeo Kistler Academy P1 Training cavity pressure P2 Sensor installation P3 Training ComoNeo P4 Training process data storage Q1 Quality in injection molding I Q2 Quality in injection molding II	Verification and function test incl. diagnostic report sensor tester e.g. 5495B/C, ComoNeo Rapid deployment of your replacement product in case of emergency Our service technician will be on site within three working days (Monday to Friday). Multiflow (max. 4 hours) Service Calibration of sensors in-house Service Calibration for ComoNeo on site or in-house DIN ISO 21001 certified Basics of cavity pressure (theory and practice), 1 day Installing cavity pressure sensors correctly (theory and practice), 1 day Working with the ComoNeo process monitoring system (theory and practice), 1 day Management and use of the process data storage solution AkvisIO IME, 1 day Quality in injection molding I, 2 days Quality in injection molding I, 3 days	44002084 44002090 44002632 44002441 44000353 Order number 44002122 In-house Order number 44002810 44002814 44002818 44002822 44002796 44002800	9968B21-D1-4 Order key 9961E-SC-04-00-0-X On-site max.8 TN Order key 44002811 44002815 44002819 44002823 44002797 44002801



For questions about our service:

Directly via QR code or via émail to: service@kistler.com

Kistler Group

Eulachstrasse 22, 8408 Winterthur Schweiz Tel.: +41 52 224 1111

www.kistler.com

Kistler Group products are protected by various intellectual property rights. For more details, visit www.kistler.com The Kistler Group includes Kistler Holding AG and all its subsidiaries in Europe, Asia, the Americas and Australia

